

WARNING! DO NOT SHINE DIRECTLY INTO EYES.

BATTERY INSTALLATION

Do not mix old and new batteries.

Do not mix Alkaline, standard or rechargeable batteries.

- 1. Unscrew the bottom of the lantern by twisting it counterclockwise. Set aside. See Diagram 1.
- 2. Insert 3 AAA batteries following the correct polarity (+, -) marked inside the battery compartment.
- 3. Place the bottom cover back on. Twist clockwise to tighten.



DIAGRAM 1

USAGE

Slowly pull up on the top part of the lantern to expose the LED lights and turn the lantern ON.

To adjust brightness: Lift up or lower the top part of the lantern*. Pull all the way up for super bright light, or pull up half way for less brightness.

* The light itself will not dim.

When not in use, press down on the top until it goes back to its compact state.



DIAGRAM 2

10 YEAR LIMITED WARRANTY

This Warranty is for the original purchaser of Bell+Howell® Taclight Mini Lantern, and is non transferable. EMSON® warrants that Bell+Howell® Taclight Mini Lantern will have no defects in material and workmanship under normal household usage for 10 years from the date of purchase. Keep the original sales receipt for proof of purchase to attain warranty provisions. Within a 10 year period from the date of purchase, EMSON® will repair or replace, on its own accord, any Bell+Howell® Taclight Mini Lantern or parts found to be defective. This warranty does not cover any shipping and handling charges which may incur. This warranty does not include any damages caused by accident, misuse, neglect, abuse, or use for commercial purposes.

If your Bell+Howell® Taclight Mini Lantern is found to be defective within the time period of this warranty, please contact the EMSON® Customer Service Department toll free number 800-423-4248. If the product is discontinued or no longer available, a replacement may be made with a similar product of equal or greater value. Any attempt to repair, or service this product on your own will void the warranty.

BELL+HOWELL® TACLIGHT™ MINI LANTERN SET OF 5 ITEM NO.7534MO
Distributed by EMSON® New York, NY 10001, USA
©2020 EMSON® All Rights Reserved. Made in China.